


LIQ /146i/2000p/B98x300/2.0" M NPT/316L/ E or N or V



Use
Spares Kit
SK-B 98x300



ACCUMULATOR DRAWING
LIQ-146i-2000p-StSt

HydroTrole Ltd

Stainless Steel Accumulators
Compare these 1965 original
gas in the bag "Bladder" type
one piece molded, no bonds or
glue, top end reservable
- no poppet valve to "jam"
Accumulators , from the
originators of the design.

Review the principle of operation
[SEE THE ANIMATION RUN](#)
A tapered cylinder, with pressure
internally will expand pro-
gressively from the large diameter
and elongate as the wall is
prevented from expanding further.
Simply because hoop stress is twice
longitudinal stress.

These stainless Accumulators of
the **LiquiFlex "SLIMLINE"** range
proven since 1965, available with
our "Flo-Thru" feature tested
by University of Eindhoven 1967.



To intercept
the water
hammer
Spikes
2 by 1" F
NPT at
45° to C
2.0" M NPT

